

# Axygen® 96-well Deep Well Microplates and Sealing Solutions

**AXYGEN**

A Corning Brand



## Features and Benefits

- ▶ Automation friendly
- ▶ Wall-to-wall technology
- ▶ Available sterile or non-sterile
- ▶ Excellent chemical resistance and withstands temperatures down to -80°C
- ▶ RNase-/DNase- free
- ▶ Nonpyrogenic
- ▶ Available with generic bar coding and individually wrapped
- ▶ Manufactured from Polypropylene (PP)

## Applications

- ▶ High throughput screening and storage applications

Clear 96-well deep well microplates (Cat. No. P-DW-20-C) are used for sample collection, *in vitro* growth chambers, and long-term storage. Axxygen deep well microplates are manufactured to stringent specifications under strict process controls and assembled via automation to ensure consistent performance and quality.

## Compatible Sealing Solutions for 96-well Deep Well Microplates

Corning Cat. No.	Description	Working Volume	Volume with Axxygen Axymat	Qty/Cs	Compatible Axxygen Axymat	Compatible Seals
P-DW-20-C	Axygen 96-well deep well microplate, 2 mL round wells, clear, non-sterile	1.8 mL	1.5 mL	50 microplates	AM-2ML-RD AM-2ML-RD-S AM-2ML-RD-IMP	PCR-AS-200, PCR-AS-600, BF-400, BF-400-S, UC-500, PCR-TS, HS-200, HS-300, HS-400
P-DW-20-C-S	Axygen 96-well deep well microplate, 2 mL round wells, clear, sterile	1.8 mL	1.5 mL	50 microplates	AM-2ML-RD AM-2ML-RD-S AM-2ML-RD-IMP	PCR-AS-200, PCR-AS-600, BF-400, BF-400-S, UC-500, PCR-TS, HS-200, HS-300, HS-400
P-DW-20-C-S-IND	Axygen 96-well deep well microplate, 2 mL round wells, clear, sterile, individually wrapped	1.8 mL	1.5 mL	50 microplates	AM-2ML-RD AM-2ML-RD-S AM-2ML-RD-IMP	PCR-AS-200, PCR-AS-600, BF-400, BF-400-S, UC-500, PCR-TS, HS-200, HS-300, HS-400



Axygen Axymat, silicone




Axygen sealing films

## Compatible Axigen® Axymat and Sealing Solution Specifications


Corning Cat. No.	Description	Type	Pierceable	Qty	Temperature
AM-2ML-RD	Pierceable sealing mat for 96-well assay microplate, round wells	Silicone Axymat	Yes	50 mats/cs	Up to -80°C freezer with H <sub>2</sub> O
AM-2ML-RD-S	Pierceable sealing mat for 96-well assay microplate, round wells, sterile	Silicone Axymat	Yes	50 mats/cs	Up to -80°C freezer with H <sub>2</sub> O
AM-2ML-RD-IMP	Chemical resistant sealing mat for 96-well assay microplates, round wells	Silicone Axymat	Yes	50 mats/cs	Up to -80°C freezer with H <sub>2</sub> O
PCR-AS-200	Pierceable, Aluminum	Aluminum sealing film	Yes	100 films/pk, 5 pk/cs	-80°C to 104°C
PCR-AS-600	Aluminum	Aluminum sealing film	Yes	100 films/pk, 5 pk/cs	-80°C to 104°C
BF-400	Rayon	Breatheable sealing film	No	100 films/pk, 5 pk/cs	-20°C to 80°C
BF-400-S	Rayon, sterile	Breatheable sealing film	No	100 films/pk, 5 pk/cs	-20°C to 80°C
UC-500	Polyolefin	Ultraclear sealing film	No	100 films/pk, 5 pk/cs	-70°C to 100°C
PCR-TS	Polyester	Tight seal film	No	100 films/pk, 5 pk/cs	-40°C to 102°C
HS-200	Polyester/Aluminum	Heat seal film	Yes	100 films/pk, 5 pk/cs	-80°C to 90°C
HS-300	Aluminum	Heat seal film	Yes	100 films/pk, 5 pk/cs	-80°C to 120°C
HS-400	Polyester/Aluminum	Heat seal film	Yes	100 films/pk, 5 pk/cs	-80°C to 40°C



Pierceable wells



Rounded bottom and wall-to-wall technology



For more specific information on claims, visit the Certificates page at [www.corning.com/lifesciences](http://www.corning.com/lifesciences).

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For additional product or technical information, visit [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 800.492.1110. Outside the United States, call +1.978.442.2200 or contact your local Corning sales office.

# CORNING

**Corning Incorporated**  
Life Sciences

836 North St.  
Building 300, Suite 3401  
Tewksbury, MA 01876  
t 800.492.1110  
t 978.442.2200  
f 978.442.2476

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

**ASIA/PACIFIC**  
Australia/New Zealand  
t 61 427286832

**China**  
t 86 21 3338 4338  
f 86 21 3338 4300

**India**  
t 91 124 4604000  
f 91 124 4604099

**Japan**  
t 81 3-3586 1996  
f 81 3-3586 1291

**Korea**  
t 82 2-796-9500  
f 82 2-796-9300

**Singapore**  
t 65 6572-9740  
f 65 6861-2913

**Taiwan**  
t 886 2-2716-0338  
f 886 2-2516-7500

**EUROPE**  
CSEurope@corning.com

**France**  
t 0800 916 882  
f 0800 918 636

**Germany**  
t 0800 101 1153  
f 0800 101 2427

**The Netherlands**  
t 020 655 79 28  
f 020 659 76 73

**United Kingdom**  
t 0800 376 8660  
f 0800 279 1117

**All Other European Countries**  
t +31 (0) 206 59 60 51  
f +31 (0) 206 59 76 73

**LATIN AMERICA**  
grupoLA@corning.com

**Brasil**  
t 55 (11) 3089-7400

**Mexico**  
t (52-81) 8158-8400